

# How many SCADA clients can be connected to an Easergy T300 using IEC 104 protocol?

There is a limitation of 8 redundant connections to create multiple SCADA channels using the IEC104 protocol. Create 1 channel per client.

Make sure to fill-in the Remote IP@ list field. It shall be different for every channel

Channel Setup

Channel  Link

Channel

Name: I104S1Chan1 Description: [ ]

Type: TCP

Specific Parameters

TCP

Mode: CALLED Remote Port: [ ]

Local Port: 2404 IP: 10 . 204 . 1 . 102

Use local IP Remote IP List: [ ]

IP: [ ]

Connect timeout: 60000 ms Reconnect time: 15000 ms

[✓] [✗]

=>

Channel Setup

Channel  Link

Channel

Name: I104S1Chan1 Description: [ ]

Type: TCP

Specific Parameters

TCP

Mode: CALLED Remote Port: [ ]

Local Port: 2404 IP: [ ]

Use local IP Remote IP List: 10.204.1.102

IP: [ ]

Connect timeout: 60000 ms Reconnect time: 15000 ms

[✓] [✗]